

Technical drawing of a 1000mm x 1000mm x 100mm plate. The plate has a 100mm x 100mm hole and a 100mm x 100mm slot. The hole is located 100mm from the top and 100mm from the left edge. The slot is located 100mm from the bottom and 100mm from the left edge. The drawing shows the plate with a 100mm x 100mm hole and a 100mm x 100mm slot. The hole is located 100mm from the top and 100mm from the left edge. The slot is located 100mm from the bottom and 100mm from the left edge. The drawing shows the plate with a 100mm x 100mm hole and a 100mm x 100mm slot. The hole is located 100mm from the top and 100mm from the left edge. The slot is located 100mm from the bottom and 100mm from the left edge.